

# rehlko



Kohler Engines  
is now Rehlko

## Command<sup>®</sup> HD Series

Gasoline Engines

### 6.75 –7.75 ft-lb Gross Torque

Our HD Series™ engines for walk-behind mowers, pressure washers and utility equipment are built to last—with 2x-longer useful engine life certified by Rehlko.\*

\* Certified by Kohler. REHLKO HD Series vs. REHLKO XT Series™ EPA Emissions Certification.



# Pass it on to *your kid*.

In a decade or so.



## BUILT TO LAST

- Based on REHLKO commercial engine designs, HD Series engines boast cast-iron cylinder liners—instead of aluminum—for added durability and engine protection. Plus premium features like platinum spark plugs, high-mount dipstick and air filter precleaner.

## WE'VE GOT YOUR BACK

- Five-year limited consumer warranty/1-year limited commercial warranty.

## RELIABLE STARTS

- Get smooth, effortless, no-prime starts thanks to our Smart-Choke™ and Easy-Pull™ technologies.

## BEAUTIFUL LAWNS

- Our Consistent-Cut™ technology maintains engine power for a cleaner cut, even in tall grass. So your lawn looks great with every cut.

## EASY FILLS, FEWER SPILLS

- Our Accu-Fill® fuel tank has a unique angled neck and a 45% larger opening for easy pours and less spilling.

MODEL		HD775	HD950	HD1100
GROSS TORQUE @ 2800 rpm	ft lb (Nm)	7.75 (10.5)	9.50 (12.9)	11 (14.9)
DISPLACEMENT	cu in (cc)	10.6 (173)	12.2 (200)	13.7 (224)
BORE	in (mma)	2.7 (70)	2.9 (73)	
STROKE	in (mm)	1.8 (45)	1.9 (48)	2.1 (53.5)
COMPRESSION RATIO		8.5:1	8.9:1	9.2:1
DRY WEIGHT	lb (kg)	26.9 (12.2)	33.5 (15.2)	
OIL CAPACITY	U.S. qt (L)	0.6 (0.6)	0.63 (0.6)	
FUEL CAPACITY	U.S. qt (L)	1.5 (1.4)	1.4	
DIMENSIONS* L x W x H	in (mm)	17.1 x 13.9 x 11 (434 x 353 x 279)	15.6 x 14.1 x 11.1 (396 x 360 x 283)	

For more information, contact your Rehiko source of supply.

Discovery Energy, LLC reserves the right to make modifications without prior notice.



[engines.rehiko.com](https://engines.rehiko.com)

Printed in Italy

E-2278

Rev.01 09/25 Eng

Discovery Energy, LLC