rehlko



Kohler Engines
is now Rehlko

Gasoline Engine Oil

Blended with an extra zinc additive, these oils help extend engine life far beyond conventional automotive oils. They are specifically formulated to protect against thermal breakdown during heavy loads and high operating temperatures.

Recommended for Command & Kohler Engines.

Why Command Genuine Oils?

- Extra zinc additive for superior wear protection and long durability
- Outperforms conventional API SN oils
- Keep engine clean for peak efficiency and reduced maintenance
- Rehlko warranty approved





OIL TYPE	Xtreme Conditions SAE 10W-30 Synthetic Blend		Xtreme Conditions SAE 20W-50 Synthetic Blend	
DESCRIPTION	Excellent all-season performance. Formulated specifically for Rehlko/Kohler engines. Standard drain interval (see owner's manual).		Added protection for higher temperature conditions. Formulated specifically for Rehlko/Kohler engines. Standard drain interval (see owner's manual).	
SIZE	CASE (12 QT)	55 GAL DRUM	CASE (12 QT)	55 GAL DRUM
PART N°	25 357 64-S	25 357 54-S	25 357 67-S	25 357 55-S





OIL TYPE	Xpert Classic SAE 30 Conventional	Xtended Life PRO SAE 10W-50 Full Synthetic Blend
DESCRIPTION	Great protection from a straight weight formula. Formulated specifically for Rehlko/Kohler engines. Standard drain interval (see owner's manual).	Best performance for all temperature conditions. Extra wear protection under extreme conditions. Up to 300-hour life with Xtended Life PRO filter.
SIZE	CASE (12 QT)	CASE (12 QT)
PART N°	25 357 02-S	25 357 72-S

For more information, contact your Rehlko source of supply.

Discovery Energy, LLC reserves the right to make modifications without prior notice.

engines.rehlko.com