

rehlko



Kohler Engines
is now Rehlko

7000 Series™

Gasoline Engines

20 – 26 hp | 14.9 – 19.4 kW

Power up your tractor or ZTR with the air-cooled, V-twin Command® engine, and run rings around your neighbors with pro-grade features, easy starts, durable components and powerful cuts.



A V-twin *beast* for backyard *warriors*.

Now with a 3-year warranty.



BUILT TO LAST

- Based on Command PRO® commercial engine design
- Pressure lubrication extends engine life by keeping critical components well-lubricated
- Upgradable oil and fuel filters provide extra protection from dirt
- Air filter options available—HD air filter is 2x larger to keep more debris out, and PRO air filter offers commercial-grade filtration and longer maintenance intervals

POWER WHEN YOU NEED IT

- Consistent-Cut™ technology maintains engine speed for a cleaner turf cut—so your lawn looks great even in tough mowing conditions

JUST TURN THE KEY AND GO

- Reliable starting, hot or cold, even at temperatures below freezing with Smart-Choke™ technology
- No need to choke the engine—starts at any throttle position
- Adds just the right amount of fuel during starting

THE BRAND YOU TRUST

- Built to last since 1920
- Engineered and assembled in the U.S.A.
- Limited 3-year consumer warranty
- With PRO air filter option: 1-year, unlimited-hour limited commercial warranty

MODEL		KT720	KT722	KT724	KT726
GROSS POWER @ 3600 rpm	max. hp (kW)	20 (14.9)	22 (16.2)	24 (17.9)	26 (19.4)
DISPLACEMENT	cu in (cc)	45 (747)			
BORE	in (mm)	3.3 (83)			
STROKE	in (mm)	2.7 (69)			
PEAK TORQUE @ rpm	ft-lb (Nm)	40.3 (54.6) @ 2200	40.4 (54.8) @ 2200	40.5 (54.9) @ 2400	42.4 (57.5) @ 2600
COMPRESSION RATIO		9.1:1			
DRY WEIGHT	lb (kg)	85 (38.6)			
OIL CAPACITY	U.S. qt (L)	2.0 (1.9)			
LUBRICATION		PRESSURE LUBRICATION WITH FULL-FLOW FILTER			
DIMENSIONS L x W x H	in (mm)	18.6 X 17.5 X 13.4 (473 X 445 X 341) WITH HD PERFORMANCE AIR FILTRATION: 18.6 X 17.5 X 13.9 (473 X 445 X 354) WITH PRO PERFORMANCE AIR FILTRATION: 18.7 X 17.5 X 15.7 (475 X 445 X 399)			

For more information, contact your Rehiko source of supply.

Discovery Energy, LLC reserves the right to make modifications without prior notice.



engines.rehiko.com

Printed in Italy

ED0035585290

Rev.02 07/25 Eng

Discovery Energy, LLC