

rehlko

Kohler Engines
is now Rehlko



Command PRO® EFI EZT Series

Gasoline Engines

25 – 27 hp | 18.6 – 20.1 kW

Introducing Command PRO® EFI EZT Series, the ultimate mower engine now with electronic fuel injection (EFI). So why EFI? It increases your uptime, reduces maintenance and starts so easy it's hard to believe.



How do you make the best better? Add EFI *technology*.



SAVES TIME AND MONEY*

- Uses significantly less fuel than a carbureted engine, saving you time and cash at the pump

PROVEN DURABILITY

- Battle-tested to meet Rehiko Command PRO® durability tests
- Cast-iron cylinder liners protect under dirty conditions

MORE RELIABLE

- Rehiko EFI technology automatically optimizes for bad fuel quality
- Starts like your car—Just turn the key and go

THE BRAND YOU CAN TRUST

- Backed with a 3-year limited commercial warranty

*Compared to a comparable Rehiko carbureted engine under comparable loads and duty cycles. Based on 600 hours of annual operation.

MODEL		EZT740	EZT750
GROSS POWER @ 3600 rpm	max. hp (kW)	25 (18.6)	27 (20.1)
DISPLACEMENT	cc (cu in)	747 (45.6)	
BORE	in (mm)	3.3 (83)	
STROKE	in (mm)	2.7 (69)	
PEAK TORQUE @ rpm	ft-lb (Nm)	40.9 (55.5) @ 2600	42.4 (57.5) @ 2800
COMPRESSION RATIO		9.0:1	
DRY WEIGHT	lb (kg)	91 (41.3)	
OIL CAPACITY	U.S. qt (L)	2.0 (1.9)	
LUBRICATION		FULL-PRESSURE LUBRICATION WITH FULL-FLOW FILTER	
DIMENSIONS L x W x H	in (mm)	STANDARD: 18.8 X 18.9 X 17 (478 X 479 X 431)	

For more information, contact your Rehiko source of supply.
Discovery Energy, LLC reserves the right to make modifications without prior notice.



engines.rehiko.com

Printed in Italy ED0035585590 Rev.01 07/25 Eng Discovery Energy, LLC