





MODEL	ENCLOSURE WEIGHT KG [LBS]	ENCLOSURE CENTER OF BALANCE
STEEL WEATHER, 15KW	163 [360]	984 [36.75]
STEEL WEATHER, 20KW		1054 [41.50]
STEEL SOUND, 15KW	172 [380]	984 [36.75]
STEEL SOUND, 20KW		1054 [41.50]
ALUMINUM SOUND, 15KW	108 [238]	984 [36.75]
ALUMINUM SOUND, 20KW		1054 [41.50]



DIMENSIONS IN [] ARE ENGLISH EQUIVALENTS

- NOTE:
- IF TANK IS ORDERED, ENCLOSURE MOUNT DIRECTLY TO TANK.
 - TANK MAY EXTEND BEYOND ENCLOSURE (DISCHARGE END ONLY)

15 MODEL 60HZ 4D3.1/4D3.8
20 MODEL 60HZ 4D3.8/4D5.0
RECON. & 600V ALTERNATORS
DIESEL KDI 1903M & 2504M

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY	DO NOT SCALE. THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001. REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.				
-	8-15-13	NEW DRAWING [CT66455]	CEK	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: XXX ± 0.25 XX ± 1.0 X ± 1.6 ANGLES ±0° 30' BEND ANGLES ± 1° SURFACE FINISH MAX. 	MAJOR  =	0		
A	3-5-14	(C-8) 162.7 WAS 127.7, 198.8 WAS 252.5 [CT73347]	CEK		CRITICAL  =	0		
B	4-17-14	(A-4) UPDATED ENGINE MFG. [CT78254]	CCL		CHARACTERISTICS COMPLY WITH KPS-80022			
C	10-3-17	(D-5) DIM. Ø50.80 [2.00] ADDED [CT177004]	SAM		SCALE: 0.05	SHEET SIZE: B	SHEET: 1 OF 1	
					TITLE: DIMENSION PRINT 15-20KW KDI ENCL			
				DRAWN: CEK	DATE:			
				APPROVED: SEE PLM SYSTEM	8-15-13	DWG NO.: ADV-8621		
THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.								

THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.