


rehlko

Command PRO® 999 cc EFI
36 – 41 hp

Built to *Dominate.*



Command PRO® EFI 999 cc Built to *Dominate*.

Why Buy?

Representing the highest level of commercial gasoline engine performance from Rehlko, the Command PRO® 999 cc EFI combines exceptional power, advanced EFI control, reinforced durability, and optimized thermal management to deliver the sustained capability required for the toughest commercial applications.

The power to own the toughest jobs.

MODEL		ECV936	ECV938	ECV941
POWER @ 3600 rpm	Max.hp (kW)	36 (26.8)	38 (28.3)	41 (30.6)
SHAFT		VERTICAL		
DISPLACEMENT	cc (cu in)	999 (61)		
BORE	in (mm)	3.5 (90)		
STROKE	in (mm)	3.1 (78.5)		
PEAK TORQUE @ rpm	ft-lb (Nm) @ 3200	54.2 (73.5) @ 3200	56.7 (76.9) @ 3200	58.9 (79.9) @ 3200
DRY WEIGHT	lb (kg)	140 (63.5)		
DIMENSIONS L x W x H	in (mm)	24.9 x 20.1 x 26.2 (633 x 510 x 666)		

Key benefits

MAXIMUM PERFORMANCE

- Up to 41 hp
- Up to 58.9 ft-lbs torque
- High power density
- Strong performance under extreme loads

BUILT FOR THE LONG HAUL

Built with premium materials and reinforced components to withstand demanding commercial duty cycles.

Advanced cooling technology helps maintain lower operating temperatures for longer engine life.

SMARTER, CLEANER TECHNOLOGY

Closed-loop EFI technology delivers:

- Improved fuel control
- Faster response
- Better efficiency
- Reliable starting

DESIGNED FOR PRODUCTIVITY

Less downtime.

More work completed.

Extended durability and simplified maintenance help maximize return throughout engine life.

The most *powerful* engine in the market

