

Xtra Performance Artic Formula

Fuel Additive

ED0035586190 EN – FR | for North America

**Description**

Rehlko All-In-One Diesel Fuel Additive provides exceptional all-season diesel engine protection by improving diesel fuel cold-flow and anti-gelling properties, increasing the cetane number and adding superior detergency and improved lubricity.

Rehlko All-In-One Diesel Fuel Additive targets internal diesel injector deposits and carbonaceous deposits, helping maintain engine performance and efficiency and reducing maintenance costs.

Benefits

- Safe for use in all diesel fuels, including biodiesel.
- Lowers cold filter-plugging point (CFPP) by up to 40°F (22°C).
- Cleans and lubricates pumps and injectors to reduce wear.
- Prevents wax settling during storage.
- Combats fuel-system corrosion.
- Increases cetane up to 4 points.
- Extends fuel-filter life.
- Alcohol-free

Applications

Use Rehlko All-In-One Diesel Additive to treat non-winter grade fuel (No 2-D North America) during the cold-weather season. This extends the operability to about 10°C (18°F) below the fuel cloud point. For operability at even lower temperature, use winter grade fuel.

Treat the fuel adding the Rehlko All-In-One Diesel Additive when outside temperature drops below 0°C (32°F). For best results, use with untreated fuel.

Additive	Maintenance up to 4-point cetane increase	Fuel Volume
	2 oz. (59.1 ml)	5 gal. (18.9 L)
	4 oz. (118.3 ml)	10 gal. (37.9 L)
	8 oz. (236.6 ml)	20 gal. (75.7 L)
	12 oz. (354.9 ml)	30 gal. (113.6 L)
	16 oz. (473.2 ml)	40 gal. (151.4 L)

Xtra Performance Artic Formula

Fuel Additive

ED0035586190 EN – FR | pour Amérique du Nord

**Description**

L'additif Rehlko All-In-One Diesel Fuel Additive offre une protection exceptionnelle du moteur diesel en toute saison en améliorant les propriétés d'écoulement à froid et anti-gélifiantes du gasoil, en augmentant l'indice de cétane et en ajoutant une détergence supérieure et un meilleur pouvoir lubrifiant.

L'additif Rehlko All-In-One Diesel Fuel Additive cible les dépôts internes des injecteurs diesel et les dépôts carbonés, favorisant le maintien des performances et le rendement du moteur et la réduction des coûts d'entretien.

Avantages

- Utilisable sans problème avec tous les carburants diesel, y compris le biodiesel.
- Abaisse la température limite de filtrabilité (CFPP) jusqu'à 40 °F (22 °C).
- Nettoie et lubrifie les pompes et les injecteurs pour réduire l'usure.
- Prévient le dépôt de paraffine pendant le stockage.
- Combat la corrosion du circuit carburant.
- Augmente le cétane jusqu'à 4 points.
- Prolonge la durée de vie du filtre à carburant.
- Sans alcool

Applications

Utilisez l'additif Rehlko All-In-One Diesel Fuel Additive pour traiter le carburant non hivernal (No 2-D North America) pendant la saison froide. Cela prolonge l'opérabilité jusqu'à environ 10 °C (18 °F) en dessous du point de trouble du carburant. Pour une opérabilité à des températures encore plus basses, utilisez du carburant hivernal.

Traitez le carburant en ajoutant l'additif Rehlko All-In-One Diesel Fuel Additive lorsque la température extérieure descend en dessous de 0 °C (32 °F). Pour de meilleurs résultats, utilisez du carburant non traité.

Additif	Entretien	Volume de carburant
	Augmentation du cétane jusqu'à 4 points	
	2 oz. (59,1 ml)	5 gal. (18,9 L)
	4 oz. (118,3 ml)	10 gal. (37,9 L)
	8 oz. (236,6 ml)	20 gal. (75,7 L)
	12 oz. (354,9 ml)	30 gal. (113,6 L)
	16 oz. (473,2 ml)	40 gal. (151,4 L)