



Gas Generators

Industrial Power Systems

Rehlko, a legacy over 100 years

In September 2024, Kohler Energy rebranded as Rehlko, marking a significant milestone in its 100-plus-year history of delivering innovative and resilient energy solutions.

Today, Rehlko is one of the largest generator manufacturers in the world, with production facilities on four continents and vast global sales, services, and distribution networks. No matter where you are, you can always count on Rehlko to deliver stability and confidence to individuals, businesses and communities.

Gas Generators 25–500 kW

Model	NG Standby (kW/kVA)	LP Standby (kW/kVA)	NG Prime (kW/kVA)	Controllers
25CCL	25/31	25/31		APM402
30CCL	30/38	30/38		APM402
40CCL	40/50	40/50		APM402
KG25	25/31	25/31		APM402
KG30	30/38	30/38		APM402
KG40A	40/50	40/50		APM402
KG40	40/50	40/50		APM402
KG45	45/56	45/56		APM402
KG50	53/66	53/66		APM402
KG60	60/75	60/75		APM402
KG80	80/100	80/100		APM402/APM603
KG100	100/125	100/125		APM402/APM603
KG125	125/156	105/131		APM402/APM603
KG150	150/188	150/188		APM402/APM603
KG180	180/225	150/188		APM402/APM603
KG200	200/250	150/188		APM402/APM603
250REZXB	260/325	170/213	230/288	APM402/APM603
300REZXC	300/375			APM402/APM603
300REZXD	300/375	210/262	270/338	APM402/APM603
350REZXD	350/438	240/300	300/375	APM402/APM603
400REZXD	400/500	295/369	360/450	APM402/APM603
450REZXD	450/562	295/369		APM402/APM603
500REZXD	500/625	295/369		APM402/APM603

Ratings based on 3-phase, 480 V
For additional technical specifications, visit powersystems.rehliko.com

Gas Generators
Custom-made to meet your needs.



KG60



KG125



KG200

The good news is that you can forget all that one-size-fits-all nonsense. Rehlko gas generators are tailored to meet your specific job requirements. Unlike most generator models, every Rehlko generator is designed to work precisely for standby, and prime applications, so you know you’re getting the right power and the right power rating—and enjoying huge cost savings along the way.

Total System Integration

We engineer every detail down to the last bolt. From generators and transfer switches to paralleling switchgear and controllers, everything works together seamlessly. Because we designed, engineered and tested it that way.

Standard Features

Tested and Approved

Rehlko generators meet tough industry testing and quality standards (UL, CSA, IBC, NFPA).

One-Step Full-Load Acceptance

Our gas generators accept full load to keep you up and running.

Ultimate Performance

Our 1800-rpm engines run quietly and efficiently to extend generator life and provide significant fuel savings.

Factory-Certified Generators

Every size Rehlko gas generator is available EPA-certified, ECM controlled, and designed to meet the latest spark-ignited emission requirements.

Versatile Power

Rehlko gas generators are made for more than just emergencies. You can use them for standby and prime applications. Because we designed, engineered and tested it that way.



For more information, contact your Rehlko source of supply.
Or call toll-free in the U.S. and Canada 800-544-2444

rehlko

powersystems.rehlko.com

G12-529 08/25 © Discovery Energy, LLC dba Rehlko