




20REOZK-C

20 kW Compact Generator

The ultimate power solution *for small spaces.*

Ideal for the telecom industry, our 20REOZK-C is built to fit in tight locations – all while packing the power you need to back up your systems for years to come.



Compact Footprint

Our reduced rectangular footprint is specially designed for cell tower platform applications, while still providing easy maintenance touch points and 48 hours of runtime.

Reliable Power

Our direct engine/alternator design eliminates the possibility of generator failure due to improper adjustment or belt breakdowns.

Single-Side Service

Maintenance is made easy with one service area. All frequently serviced touch points are located on the same side and accessible by easy-to-remove doors.

Quiet Performance

Our sound enclosure delivers a sound performance of 65 dBA – which is among the quietest available.

Model	20REOZK-C Standard Tank	20REOZK-C State Tank
Engine Make	Rehiko KDI	
Number of Cylinders	4 inline	
Displacement, L (cu. in.)	2.5 (158)	
Operating Speed (rpm)	1800	
Controller	APM402	
Voltage	120/240, single phase	
Breaker	100 A	
Alternator	Poles: 4 Bearing: 1, sealed Voltage Regulator: digital, integrated Steady State Voltage Regulation: ± 0.5% Insulation: NEMA MG1, Class H	
Sound Enclosure	Steel with Stainless Steel Hardware – 65 dBA	
Tank Gallons/48 Hrs @ Full Load	105	105
Footprint Dimensions, L x W x H, mm (in)	1473.2 x 762.0 x 2253.0 (58.0 x 30.0 x 88.7)	1473.2 x 762.0 x 2430.8 (58.0 x 30.0 x 95.7)
Overall Dimensions, L x W x H, mm (in) including spill box		1846.6 x 812.8 x 2430.8 (72.7 x 32.0 x 95.7)
Weight (lbs)	2,164	2,250
Diesel Fuel Consumption – Standby, Lph (gph) at % Load	100% 7.2 (1.9) 75% 5.7 (1.5) 50% 3.8 (1.0)	
State Tank Options Included		5-Gallon Spill Containment High Fuel Level Switch with Alarm

