




Meet the New KD Series™ 80–300 kW



The new KD Series™ represents the next evolution of Rehlko's engineering. Extensively tested and globally supported, it delivers dependable power where failure isn't an option.



The all-new KD Series™ addition delivers unmatched dependability, setting the benchmark for a *new era of reliability*.

Rigorously tested beyond industry standards, it delivers proven reliability, thousands of site-ready configurations, and consistent global performance with local support—all while protecting long-term value.

Fully Integrated Rehlko System

Rehlko's KD Series delivers a premium, fully integrated system built with world-class components. Designed to meet ISO8528-5 G3 load acceptance performance, it ensures rapid response and dependable performance. Ready to start when the grid stops.

Unmatched Build Quality

Rehlko enclosures are built from thick-gauge steel or aluminum and protected by our Power Armor™ finish for corrosion resistance and long-term durability. The result is lasting strength, superior protection, and the confidence to perform anywhere.

Short Lead Time

These configurable products are engineered for efficiency, leveraging standardized designs and shared components to deliver shorter, more predictable lead times. You get the performance and flexibility you need without the wait.

Next-Generation Testing

Every model is prototyped and tested in our labs for thermal balance, noise levels, electrical safety, vibration and long-term performance. Nothing leaves without proving itself.

Thousands of Ways. One *Standard of Reliability*.

Extensive configuration options available, including voltage, frequency, enclosures, control systems, and modular accessories—built to match your site needs. Easily configured to meet regional codes, standards, and certification requirements.

Optimized Package

The range and the preconfigured equipment have been designed to allow you to benefit from the best value for money and to optimize your investment.

Premium Parts & Services. Wherever You Are.

Tailored service contracts and extended warranty included to ensure long-term reliability and built-in support.

With numerous direct service locations and 220+ distributors worldwide, Rehlko customers have the assurance of 24/7 emergency service and responsive after-market support.

Model	Standby 60 Hz (kW/kVA)	Engine Manufacturer	Engine Details	Enclosure Dimension (Inches)	Tank Options	Sound Levels dBA*	EPA Tier	Controllers
KD80	80/100	Rehlko	4.5L 4 Cylinder 1800 rpm	126 x 46 x 65	24hr (standard/state)	70	Tier 3	APM402/ APM603
KD100	100/125				48hr (standard/state)	70		
KD130	130/163				96hr (state)	70		
KD150	150/188	Rehlko	6.7L 6 Cylinder 1800 rpm	148 x 53 x 79	24hr (standard/state)	71	Tier 3	APM402/ APM603
KD180	180/225				48hr (standard/state)	72		
KD200	200/250				96hr (state)	72		
KD230	230/288	Rehlko	8.9L 6 Cylinder 1800 rpm	162 x 53 x 79	24hr (standard/state)	75	Tier 3	APM402/ APM603
KD250	250/313				48hr (standard/state)	75		
KD275	275/344				96hr (state)	75		
KD300	300/375					75		

*Measured at 7m with sound enclosure (100% load)



Contact Us
powersystems.rehlko.com

G12-625 12/25 © Discovery Energy, LLC dba Rehlko