




8			7				6		5
MODEL	CAPACITY		WEIGHT		LENGTH		HEIGHT		EMERGENCY VENT (A) INNER/OUTER
	LITERS	GAL	KG	LBS	MM	IN	MM	IN	IN
10/30kW	301	80	208	459	1935.0	76.2	431.8	17.0	3/3
10/30kW	465	123	266	586	1935.0	76.2	635.0	25.0	3/3
10/30kW	622	164	315	695	1935.0	76.2	812.8	32.0	3/3
10/30kW	791	209	362	798	2070.1	81.5	914.4	36.0	3/3



NOTE:
FOR FURTHER TANK DETAIL
SEE INDIVIDUAL DRAWINGS

■ 4X Ø25.4 [1.00]
STANDARD MOUNTING

REV

DATE

ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL
□ INDICATES PART NUMBERS AFFECTED BY LATEST
DRAWING REVISION

-

11-11-13

NEW DRAWING [CT63958]

A

7-22-15

(D-7) 152.4 [6.00] STUB UP DIMENSION
ADDED [CT119088]

B

11-18-15

SEE SHEET 2 [CT131976]

BY

SDS

SAK

SSS

THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001.
REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.

UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS IN MILLIMETERS
GENERAL TOLERANCES: N/A

DRAWN: SDS

DATE: 11-11-13

APPROVED: SEE PLM
SYSTEM

DO NOT SCALE.

MAJOR ○ = 0

CRITICAL ⊙ = 0

CHARACTERISTICS COMPLY
WITH KPS-80022

SCALE: 0.08

SHEET SIZE: B

SHEET: 1 OF 2

TITLE:
DIMENSION PRINT

DWG NO.: ADV-8643

rehlko

THIRD ANGLE PROJECTION

THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.

TANK FITTINGS:
A. A" NPT EMERGENCY VENT FITTING PER NFPA 30
WITH VENT CAPS (QTY 2).
B. 2" NPT FUEL FILL FITTING WITH LOCKABLE CAP
AND 2" RISER.
D. 2" NPT NORMAL VENT FITTING WITH MUSHROOM VENT
CAP AND 3" RISER.
E. 1/2" NPT FITTING FOR REMOVABLE ENGINE SUPPLY
DIP TUBE (3/8" NPT FEMALE WITH CHECK VALVE).
F. 1/2" NPT FITTING FOR REMOVABLE FUEL RETURN
DIP TUBE (3/8" NPT FEMALE).
H. 2" NPT FOR FUEL LEVEL SENDING UNIT.
M. 1/2" NPT BASIN DRAIN
(INSTALL STEEL 1/2" NPT PIPE PLUG).
N. 1/2" NPT FOR FUEL IN BASIN SWITCH.

