

rehlko

Kohler Engines
is now Rehlko




Command PRO® 999 cc

Gasoline Engines

32.5 – 41 hp | 24.2 – 30.6 kW

The Command PRO® EFI engine saves gas and reduces downtime, giving you the power to cut costs and cover more ground every day.



Command PRO® 999 cc

The *muscle* you need for commercial applications

Whatever the job or power range, the **Command PRO® 999 cc engine**—available in **carbureted** models from **32.5 to 37 horsepower** and **EFI (Electronic Fuel Injection)** models from **36 to 41 horsepower**—redefines what a gasoline engine can do. Engineered for high-demand applications, it delivers **exceptional horsepower, torque, and long-term reliability.**

Designed for Durability

Featuring the latest in engine cooling technology, this powerhouse is built to run cooler, last longer, and perform stronger—no matter the conditions.

Peak Performance Across the Range

From landscaping to industrial equipment, the Command PRO® 999 cc delivers consistent, high-output performance that professionals trust.



Crafted with premium materials and a rugged design, our engines are built to last. Fewer service intervals and simplified maintenance mean more uptime and lower operating costs.

High Torque. Reliable Output.
Efficient Fuel Use.



Advanced combustion systems reduce fuel consumption and emissions, helping you meet environmental standards without sacrificing power. It's performance with a conscience.

Smarter, Cleaner Technology



With optimized fuel use, reduced maintenance, and long-lasting reliability, our engines deliver exceptional value over their lifetime.

Built for the Long Haul

Lower Total Cost of Ownership.
Higher ROI.

Command PRO® EFI 999 cc

Standard features

Clean-Spin™ Dripless Oil Change – Faster, Cleaner, Less Maintenance

Integrated oil cooler ensures lower operating temperatures, enhancing engine performance and longevity

Electronic fuel injection and spark control coupled with Electronic Throttle Body (ETB)

Engineered with fully sealed electrical connections to safeguard sensitive components from moisture and corrosion, ensuring reliable performance over time

Largest in class, 6 inch heavy-duty air filter, with carbon based inner safety filter and debris ejection system, **extends service intervals up to 600 hours**

Optimized combustion enables extended spark plug service intervals—up to **600 hours**

20-Amp sealed charging with over-voltage protection

Large, easy-to-remove cleanout covers

High-efficiency fan, guard, and rotating grass screen for superior debris management

Full-pressure lubrication with filter and Oil Sentry™

Hardened crank journals for long-life

12-volt solenoid shift starter

3-Year limited warranty

Variable timing electronic ignition

EMC and RFI compliant

1 1/8-inch diameter crankshaft

Large capacity 10-micron fuel filter

Automotive style head gasket delivers long life and reduced oil consumption

Hydraulic lifters for automatic valve lash adjustment – eliminates manual adjustments, and ensures optimal performance over the life of the engine

Easily accessible service points

Popular factory options

25-Amp Sealed charging system

Canister mufflers with right, left, or center outlets

Analog or CAN Bus control


Proprietary analog speed controller—mounts directly to engine for repowers or integrates seamlessly with machine throttle

Chopper-type grass screen




Command PRO® EFI

36–41 HP Horizontal-Shaft Engines




Low profile air cleaner
Flywheel view




Low profile air cleaner
Fuel Pump side view

Data

Dimensions mm [in]




Heavy duty air cleaner
Flywheel view



Heavy duty air cleaner
Fuel Pump side view


MODEL		ECH936	ECH938	ECH941
POWER @ 3600 rpm	Max.hp (kW)	36 (26.8)	38 (28.3)	41 (30.6)
SHAFT		HORIZONTAL		
DISPLACEMENT	cc (cu in)	999 (61)		
BORE	mm (in)	90 (3.5)		
STROKE	mm (in)	78.5 (3.1)		
PEAK TORQUE @ rpm	ft-lb (Nm)	54.2 (73.5) @ 3200	56.7 (76.9) @ 3200	58.9 (79.9) @ 3200
COMPRESSION RATIO		9.3:1		
DRY WEIGHT	lb (kg)	132 (60)		
OIL CAPACITY	U.S. qt (L)	2.0 (1.9)		
LUBRICATION		FULL-PRESSURE WITH FULL-FLOW FILTER		
DIMENSIONS L×W×H	in (mm)	LOW-PROFILE AIR CLEANER 17.1 X 19.1 X 23.8 (435 X 559 X 604) HEAVY-DUTY AIR CLEANER 17.1 X 22 X 31 (435 X 559 X 789)		

Maximum power



— ECH936
— ECH938
— ECH941

Maximum torque



— ECH936
— ECH938
— ECH941

Command PRO® 999 cc

Standard features

Hydraulic valve lifters for quiet operation, no adjustments

High-efficiency fan and screen for superior cooling and longer engine life

15-Amp charging, regulated

Front-mount controls for easy operation and OEM installation

Easily accessible service points

Full-pressure lubricant with filter and Oil Sentry™ automatic low-oil/shutdown system

Large dual drains for faster oil changes

Hardened crank journals for long-life 12-volt solenoid shift starter

3-Year limited warranty

Electronic ignition with high-performance spark plugs

Solenoid fuel shutdown to limit afterbang

Popular factory options

Canister mufflers with right, left and center outlets

Guard for rotating grass screen

Engine-mounted controls (CH models)

Remote oil filter exhaust deflector

Spark arrestor

20- and 25-Amp charging systems

11/8- and 17/16-inch crankshaft diameters

Front drive shaft

Customer mounting pilot (CH models)


EMC and RFI-compliant

Chopper-type grass screen




Command PRO[®]

32.5–37 HP Horizontal-Shaft Engines*




Front view




PTO view

Data

Dimensions mm [in]



Starter side view




Fuel pump side view

MODEL		CH940	CH980	CH1000
POWER @ 3600 rpm	Max.hp (kW)	32.5 (24.2)	35 (26.1)	37 (27.5)
DISPLACEMENT	cc (cu in)		999 (61)	
BORE	mm (in)		90 (3.5)	
STROKE	mm(in)		78.5 (3.1)	
PEAK TORQUE @ rpm	ft-lb (Nm)	53.5 (71.8) @ 2600	54.3 (73.6) @ 3400	57.4 (77.8) @ 3200
COMPRESSION RATIO			8.8:1	
DRY WEIGHT	lb (kg)		131 (60)	
OIL CAPACITY	U.S. qt (L)		2.0 (1.9)	
LUBRICATION		FULL-PRESSURE LUBRICATION WITH FULL-FLOW FILTER		
DIMENSIONS L x W x H	in (mm)	LOW-PROFILE AIR CLEANER 15.8 X 19.1 X 23.6 (402 X 484 X 600) HEAVY-DUTY AIR CLEANER 17.1 X 19.1 X 27.5 (435 X 484 X 699)		


* With Heavy-Duty Air Cleaner

Maximum power



— CH940
— CH980
— CH1000

Maximum torque



— CH940
— CH980
— CH1000

For more information, contact your Rehlko source of supply.

Discovery Energy, LLC reserves the right to make modifications without prior notice.

engines.rehiko.com

