


rehlko



Kohler Engines
is now Rehlko

Command PRO® EFI

Gasoline Engines

26.8 – 28.3 kW | 36 – 38 hp

The Command PRO® EFI 999 cc engine redefines what a gasoline engine can do. Engineered for high-demand applications, it delivers exceptional horsepower, torque, and long-term reliability.



Command PRO® 999 cc

Power that *performs*. Reliability that *lasts*.

Whatever the job or power range, the **Command PRO® 999 cc engine**—available in models from **36 – 38 horsepower**—redefines what a gasoline engine can do. Engineered for high-demand applications, it delivers **exceptional horsepower, torque, and long-term reliability**.

Redesigned for Durability

Featuring the latest in engine cooling technology, this powerhouse is built to run cooler, last longer, and perform stronger—no matter the conditions.

Peak Performance Across the Range

From landscaping to industrial equipment, the Command PRO® 999 cc delivers consistent, high-output performance that professionals trust.



BUILT FOR THE LONG HAUL
Crafted with premium materials and a rugged design, our engines are built to last.

LOWER TOTAL COST OF OWNERSHIP. HIGHER ROI.
Fewer service intervals and simplified maintenance mean more uptime and lower operating costs.



HIGH TORQUE. RELIABLE OUTPUT. EFFICIENT FUEL USE.
With optimized fuel use, reduced maintenance, and long-lasting reliability, our engines deliver exceptional value over their lifetime.



SMARTER, CLEANER TECHNOLOGY
Advanced combustion systems reduce fuel consumption and emissions, helping you meet environmental standards without sacrificing power. It's performance with a conscience.

Command PRO[®] 999_{cc}

Standard features

Easily accessible service points

Clean-Spin™ Dripless Oil Change –
Faster, Cleaner, Less Maintenance

Integrated oil cooler ensures lower
operating temperatures, enhancing
engine performance and longevity

Electronic fuel injection and
spark control coupled with engine
throttle body (ETB)

Engineered with fully sealed
electrical connections to safeguard
sensitive components from
moisture and corrosion, ensuring
reliable performance over time

6-Inch heavy-duty air filter (largest
in class) with carbon based inner
safety filter, and debris dirt ejection
system to **extend service intervals
up to 600 hours**

Optimized combustion enables
extended spark plug service
intervals—up to **600 hours**

20 A sealed charging regulated with
over-voltage protection

Easily removable cleanout covers

High-efficiency fan system with
superior debris management
Guard for rotating grass screen

Full-pressure lubricant with filter
and Oil Sentry™

Hardened crank journals for long-life

12-volt solenoid shift starter

3-Year limited warranty

Variable timing electronic ignition

EMC and RFI compliant

1 1/8-Inch diameter crankshaft

Large capacity 10-micron fuel filter

Automotive style head gasket
interface to deliver long life and
reduced oil consumption

Hydraulic valve lifters for quiet
operation, no adjustments


Popular factory options

25 A Sealed charging system

Canister mufflers with right, left
outlets

Analog or CAN Bus control

Proprietary analog speed controller—
mounts directly to engine for
repowers or integrates seamlessly
with machine throttle.




Command PRO® EFI

36–38 HP Verical–Shaft Engines*




Back view




Side view

Data

Dimensions (mm)



Back view




Side view


MODEL		ECV936	ECV938
POWER @ 3600 rpm	Max.hp (kW)	36 (26.8)	38 (28.3)
SHAFT		VERTICAL	
DISPLACEMENT	cc (cu in)	999 (61)	
BORE	in (mm)	3.5 (90)	
STROKE	in (mm)	3.1 (78.5)	
PEAK TORQUE @ rpm	ft-lb (Nm)	54.2 (73.5) @ 3200	56.7 (76.9) @ 3200
COMPRESSION RATIO		8.8:1	
DRY WEIGHT	lb (kg)	140 (63.5)	
OIL CAPACITY	U.S. qt (L)	2.5 (1.9)	
LUBRICATION		FULL-PRESSURE WITH FULL-FLOW FILTER	
DIMENSIONS L×W×H	in (mm)	24.9 X 20.1 X 26.2 (633 X 510 X 666)	

* With Heavy–Duty Air Cleaner

Maximum power



Maximum torque





For more information, contact your Rehko source of supply.
Discovery Energy, LLC reserves the right to make modifications without prior notice.

engines.rehko.com

ED0035586270 Rev.00 09/25 EN Discovery Energy, LLC