

MODEL	GENSET WEIGHT (WET) WITH ENCLOSURE		ENCLOSURE ONLY
	STEEL WEATHER	3942 Kg [8690 LBS]	
	STEEL SOUND	3969 Kg [8750 LBS]	
250 4UA10/4UA13, 300 4UA13	ALUMINUM SOUND	3647 Kg [8040 LBS]	454 Kg [1000 LBS]

D

C

B





A

D

C

B

A



300/250 MODEL, 4UA10/4UA13
RECONNECTABLE
IMPROVED MOTOR STARTING (IMS) RECONNECTABLE
& 600 VOLT ALTERNATORS
14.6 LITER DOOSAN

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY	DO NOT SCALE. THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001. REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.		MAJOR ○ = 0 CRITICAL ● = 0		THIRD ANGLE PROJECTION	
C	9-28-12	(A-3) 95 WAS 50, 800 WAS 1159 (A-2) 2232 WAS 1919 [CT25241]	SAM	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A		CHARACTERISTICS COMPLY WITH KPS-80022		SCALE: 0.03	
D	2-18-13	UPDATED TO NEW DECALS [CT32175]	SAM			SHEET SIZE: B		SHEET: 1 OF 1	
E	9-27-17	(D-7) DIM. Ø100.8 [3.97] ADDED [CT177004]	SRM			DRAWN: KDW		DATE: 9-11-09	
F	03-07-18	(C,D-4)2504UA10/4UA13,3004UA13 WAS 2504UA10/4UA13; (A-4) 300/250 WAS 250 [CT184844]	SRB	APPROVED: SEE PLM SYSTEM		TITLE: DIMENSION PRINT, ENCLOSURE		DWG NO.: ADV-7718	
G	9-6-18	(B-7) C.O.B ADDED [CT189264]	APB						

THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.