








NOTE: DIMENSIONS IN [] ARE
ENGLISH STANDARD EQUIVALENTS

GENSET WEIGHT:
MAX WEIGHT (WET): 3200 KG [7040 LBS]
(LESS ACCESSORIES)

300/250 MODEL, 4UA10/4UA13
RECONNECTABLE,
IMPROVED MOTOR STARTING (IMS) RECONNECTABLE
& 600 VOLT ALTERNATORS
14.6 LITER DOOSAN, EPA/NON-EPA

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY	DO NOT SCALE. THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001. REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.					
E	21JUL2025	(C,B-5,4,3,2) 1453.9 [57.24] WAS 1455.0		UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A		MAJOR  =	0	 THIRD ANGLE PROJECTION	
		[57.28], 1783 [70.2] WAS 1777 [70.0], 1790				CRITICAL  =	0		
		[70.5] WAS 1767 [69.6], 700 [27.6] WAS 694				CHARACTERISTICS COMPLY WITH KPS-80022			
		[27.3], 1400 [55.1] WAS 1387 [54.6], 1538 [60.6]				SCALE: 0.04	SHEET SIZE: B		SHEET: 1 OF 4
		WAS 1534 [60.4], 184 [7.2] WAS 178 [7.0]; SEE SHEET 4	MBM			TITLE: DIMENSION PRINT, 250/300 REZX			
				DRAWN: AWK	DATE:				
				APPROVED: SEE PLM SYSTEM	1-14-11	DWG NO.: ADV-7987			
THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.									






**DETAIL A
EXHAUST OUTLETS
SCALE 0.35**

NOTE: DIMENSIONS IN [] ARE
ENGLISH STANDARD EQUIVALENTS

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY	DO NOT SCALE. THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001. REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.		
D	2-20-19	(C-2,3) DETAIL A EXHAUST OUTLETS NOTE ADDED; (C-1) Ø90 [3.5] ADDED; SEE SHEET 1 [CT191938]	DS	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A	MAJOR ○ = 0 CRITICAL ⦿ = 0	THIRD ANGLE PROJECTION
E	21JUL2025	SEE SHEET 1 & 4	MBM		CHARACTERISTICS COMPLY WITH KPS-80022	
				DRAWN: AWK	DATE: 1-14-11	SCALE: 0.04 SHEET SIZE: B SHEET: 2 OF 4
				APPROVED: SEE PLM SYSTEM		TITLE: DIMENSION PRINT, 250/300 REZX
						DWG NO.: ADV-7987

300/250 MODEL, 4UA10/4UA13
RECONNECTABLE,
IMPROVED MOTOR STARTING (IMS) RECONNECTABLE
& 600 VOLT ALTERNATORS
14.6 LITER DOOSAN, EPA/NON-EPA

THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.





300/250 MODEL, 4UA10/4UA13
RECONNECTABLE,
IMPROVED MOTOR STARTING (IMS) RECONNECTABLE
& 600 VOLT ALTERNATORS
14.6 LITER DOOSAN, EPA/NON-EPA



NOTE: DIMENSIONS IN [] ARE
ENGLISH STANDARD EQUIVALENTS

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY	DO NOT SCALE. THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001. REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.				
B	8-18-14	SEE SHEET 1 [CT89357]	SAK	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A	MAJOR ⌀ = 0		THIRD ANGLE PROJECTION 	
C	03-07-18	(A-4) 300/250 WAS 250 [CT184844]	SRB		CRITICAL ⚡ = 0			
D	2-20-19	SEE SHEET 1 & 2 [CT191938]	DS		CHARACTERISTICS COMPLY WITH KPS-80022			
E	21JUL2025	SEE SHEET 1 & 4	MBM		SCALE: 0.04 SHEET SIZE: B			
				DRAWN: AWK	DATE:	TITLE: DIMENSION PRINT, 250/300 REZX		
				APPROVED: SEE PLM SYSTEM	1-14-11	DWG NO.: ADV-7987		
THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.								

THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.



ENGINE BLOCK HEATER CROSSMEMBER MOUNTING ARRANGEMENT



ENGINE BLOCK HEATER SIDEMEMBER MOUNTING ARRANGEMENT

300/250 MODEL, 4UA10/4UA13
RECONNECTABLE,
IMPROVED MOTOR STARTING (IMS) RECONNECTABLE
& 600 VOLT ALTERNATORS
14.6 LITER DOOSAN, EPA/NON-EPA

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY	DO NOT SCALE. THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001. REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.		
E	21JUL2025	SHEET 4 ADDED FOR BLOCK HEATER DETAILS; SEE SHEET 1	MBM	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: XX ± 0.25 X ± 1.0 X ± 1.5 ANGLES ± 0° 30' BEND ANGLES ± 1°		
				SURFACE FINISH MAX.		
				DRAWN: AWK	DATE:	
				APPROVED: SEE PLM SYSTEM	1-14-11	
THIS DRAWING IN DESIGN AND DETAIL IS DISCOVERY ENERGY, LLC PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH DISCOVERY ENERGY, LLC WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.				THIRD ANGLE PROJECTION		
				SCALE: 0.04 SHEET SIZE: B SHEET: 4 OF 4		
				TITLE: DIMENSION PRINT, 250/300 REZX		
				DWG NO.: ADV-7987		