


Industrial Diesel Generator Set

KD1500

Tier 2 EPA-Certified for Stationary Emergency Applications



KDxxxx designates a generator set with a Tier 2 EPA-Certified engine. KDxxxx-F designates a 60 Hz generator set with a fuel optimized engine.

Ratings Range

60 Hz

Standby: kW 1300-1500

kVA 1625-1875

Prime: kW 1150-1350

kVA 1438-1688



Standard Features

- Rehlko provides one-source responsibility for the generating system and accessories.
- Approved for use with certified renewable Hydrotreated Vegetable Oil (HVO)/Renewable Diesel (RD) fuels compliant with EN15940/ASTM D975.
- The generator set and its components are prototype-tested, factory-built, and production-tested.
- The 60 Hz generator set offers a UL 2200 listing.
- · The generator set accepts rated load in one step.
- The 60 Hz generator set meets NFPA 110, Level 1, when equipped with the necessary accessories and installed per NFPA standards.
- A standard three-year unlimited-hour limited warranty for standby applications in the U.S. And Canada. Five-year basic, five-year comprehensive, and ten-year extended limited warranties are also available.
- A standard two-year or 8700-hour limited warranty for prime power applications.
- Other features:
 - Rehlko designed controllers for one-source system integration and remote communication. See Controllers on page 4.
 - The low coolant level shutdown prevents overheating (standard on radiator models only).

General Specifications

Orderable Generator Model Number	GMKD1500
Manufacturer	Rehlko
Engine: model	KD45V20
Alternator Choices	KH03850TO4D
	KH04590TO4D
	KH04920TO4D
	KH05641TO4D
	KH05740TO4D
	KH06721TO4D
	KH06810TO4D
Performance Class	Per ISO 8528-5
One Step Load Acceptance	100%
Voltage	Wye, 600 V., or 4160 V
Controller	APM603, APM802
Fuel Tank Capacity, L (gal.)	5863-21985 (1549-5808)
Fuel Consumption, L/hr (gal./hr) 100% at Standby	401 (105.9)
Fuel Consumption, L/hr (gal./hr) 100% at Prime Power	371 (98.0)
Emission Level Compliance (KDxxxx)	Tier 2
Open Unit Noise Level @ 7 m dB(A) at Rated Load	97
Data Center Continuous (DCC) Rating (Refer to TIB-101 for definitions)	Same as the Standby Rating below

Conscious Care™ Qualified

 Reduce operating costs, fuel consumption, and greenhouse gas emissions with Conscious Care™ maintenance program.

Generator Set Ratings

				150°C Rise Standby Rating		130°C Rise Standby Rating		125°C Rise Prime Rating		105°C Rise Prime Rating	
Alternator	Voltage	Ph	Hz	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps
KH03850TO4D	240/416	3	60	1320/1650	2290	1300/1625	2255	1280/1600	2221	1150/1438	1996
KH03030104D	277/480	3	60	1500/1875	2256	1500/1875	2256	1350/1688	2031	1300/1625	1955
KH04590TO4D	240/416	3	60	1430/1788	2482	1410/1762	2446	1350/1688	2343	1260/1575	2186
KH04390104D	277/480	3	60	1500/1875	2256	1500/1875	2256	1350/1688	2031	1350/1688	2031
	230/400	3	60	1500/1875	2707	1500/1875	2707	1350/1688	2437	1350/1688	2437
KH04920TO4D	240/416	3	60	1500/1875	2603	1500/1875	2603	1350/1688	2343	1350/1688	2343
	277/480	3	60	1500/1875	2256	1500/1875	2256	1350/1688	2031	1350/1688	2031
	220/380	3	60	1500/1875	2849	1500/1875	2849	1350/1688	2565	1350/1688	2565
	230/400	3	60	1500/1875	2707	1500/1875	2707	1350/1688	2437	1350/1688	2437
KH05740TO4D	240/416	3	60	1500/1875	2603	1500/1875	2603	1350/1688	2343	1350/1688	2343
	277/480	3	60	1500/1875	2256	1500/1875	2256	1350/1688	2031	1350/1688	2031
	347/600	3	60	1500/1875	1805	1500/1875	1805	1350/1688	1625	1350/1688	1625

RATINGS: All three-phase units are rated at 0.8 power factor. Standby Ratings: The standby rating is applicable to varying loads for the duration of a power outage. There is no overload capability for this rating. Prime Power Ratings: At varying load, the number of generator set operating hours is unlimited. A 10% overload capacity is available for one hour in twelve. Ratings are in accordance with ISO-8528-1 and ISO-3046-1. For limited running time and continuous ratings, consult the factory. Obtain technical information bulletin (TIB-101) for ratings guidelines, complete ratings definitions, and site condition derates. The generator set manufacturer reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever.



Industrial Diesel Generator Set - KD1

Tier 2 EPA-Certified for Stationary Emergency Applications

				150°C Rise Standby Rating		130°C Rise Standby Rating		125°C Rise Prime Rating		105°C Rise Prime Rating	
Alternator	Voltage	Ph	Hz	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps
	220/380	3	60	1500/1875	2849	1500/1875	2849	1350/1688	2565	1350/1662	2565
	230/400	3	60	1500/1875	2707	1500/1875	2707	1350/1688	2437	1350/1688	2437
KH06810TO4D	240/416	3	60	1500/1875	2603	1500/1875	2603	1350/1688	2343	1350/1688	2343
	277/480	3	60	1500/1875	2256	1500/1875	2256	1350/1688	2031	1350/1688	2031
	347/600	3	60	1500/1875	1805	1500/1875	1805	1350/1688	1625	1350/1662	1625
KH05641TO4D	2400/4160	3	60	1500/1875	261	1500/1875	261	1340/1675	233	1340/1675	233
KH06721TO4D	2400/4160	3	60	1500/1875	261	1500/1875	261	1340/1675	233	1340/1675	233

Engine Specifications	60 Hz				
Engine: model	KD45V20				
Engine: type	4-Cycle, Turbocharged, Intercooled				
Cylinder arrangement	20-V				
Displacement, L (cu. in.)	45 (2746)				
Bore and stroke, mm (in.)	135 x 157 (5.31 x 6.18)				
Compression ratio	15.0:1				
Piston speed, m/min. (ft./min.)	565 (1854)				
Main bearings: quantity, type	11, Precision Half Shells				
Rated rpm	1800				
Max. power at rated rpm, kWm (BHP)	1654 (2218)				
Cylinder head material	Cast Iron				
Crankshaft material	Steel				
Valve (exhaust) material	Steel				
Governor: type, make/model	KODEC Electronic Control				
Frequency regulation, no-load to full-load	Isochronous				
Frequency regulation, steady state	±0.25%				
Frequency	Fixed				
Air cleaner type, all models	Dry				
Lubricating System	60 Hz				
Туре	Full Pressure				
Oil pan capacity with filter (dipstick max.					
mark), L (qt.)§	165 (174)				
Oil pan capacity with filter (initial fill),					
L (qt.)§	180 (190)				
Oil filter: quantity, type§	4, Cartridge				
Oil cooler	Water-Cooled				
§ Rehlko recommends the use of Rehlko Genuine oil and filters.					
Fuel System	60 Hz				

Fuel System	60 Hz
Fuel supply line, min. ID, mm (in.)	19 (0.75)
Fuel return line, min. ID, mm (in.)	12 (0.5)
Max. fuel flow, Lph (gph)	555 (147)
Min./max. fuel pressure at engine supply connection, kPa (in. Hg)	-30/30 (-8.8/8.8)
Max. return line restriction, kPa (in. Hg)	30 (8.8)
Fuel filter: quantity, type	1, Primary Engine Filter
	1, Fuel/Water Separator
Recommended fuel	#2 Diesel ULSD/HVO/RD

Fuel Consumption**	60 Hz				
Diesel, Lph (gph) at % load	Standby Rating				
100%	401 (105.9)				
75%	316 (83.5)				
50%	222 (58.6)				
25%	124 (32.8)				
Diesel, Lph (gph) at % load	Prime Rating				
100%	371 (98.0)				
75%	287 (75.8)				
50%	203 (53.6)				
25%	119 (31.4)				
** Volumetric Fuel consumption is up to 4% higher when using					

** Volumetric Fuel consumption is up to 4% higher when using HVO/RD than #2 ULSD.

Radiator System	60 Hz
Ambient temperature, °C (°F) *	50 (122)
Engine jacket water capacity, L (gal.)	143 (37)
Radiator system capacity, including engine,	
L (gal.)	278 (73.4)
Engine jacket water flow, Lpm (gpm)	2339 (618)
Heat rejected to cooling water at rated kW,	
dry exhaust, kW (Btu/min.)	623 (35429)
Heat rejected to charge air cooler at rated	
kW, dry exhaust, kW (Btu/min.)	454 (25818)
Charge cooling air inlet temperature at	
25°C (77°F) ambient, °C (°F)	229 (444)
Turbocharger boost (abs), bar (psi)	3.45 (50.0)
Water pump type	Centrifugal
Fan diameter, including blades, mm (in.)	1750 (68.9)
Fan, kWm (HP)	70 (93.9)
Max. restriction of cooling air, intake and	
discharge side of radiator, kPa (in. H ₂ O)	0.125 (0.5)

 Enclosure with enclosed silencer reduces ambient temperature capability by 5°C (9°F).

Remote Radiator System†	60 Hz
Exhaust manifold type	Dry
Connection sizes:	
Water inlet/outlet, mm (in.)	_
Charge air cooler inlet/outlet	_
(pipe dia. of flange), mm (in.)	
Static head allowable above engine,	
kPa (ft. H₂O)	70 (23.5)

[†] Contact your local distributor for cooling system options and specifications based on your specific requirements.



Industrial Diesel Generator Set - KD

Tier 2 EPA-Certified for Stationary Emergency Applications

Exhaust System	60 Hz
Exhaust flow at rated kW, m³/min. (cfm)	331 (11689)
Exhaust temperature at rated kW at 25°C (77°F) ambient, dry exhaust, °C (°F)	502 (935)
Maximum allowable back pressure, kPa (in. Hg) Exh. outlet size at eng. hookup, mm (in.)	8.5 (2.5) See ADV drawing
<u> </u>	60 Hz
Electrical System	00 HZ
Battery charging alternator: Ground (negative/positive) Volts (DC) Ampere rating	Negative 24 140
Starter motor qty. at starter motor power rating, rated voltage (DC)	Standard: 2 @ 8.4 kW, 24; Redundant (optional): 4 @ 8.4 kW, 24
Battery, recommended cold cranking amps (CCA):	
Quantity, CCA rating each, type (with standard starters)	4, 1110, AGM
Quantity, CCA rating each, type (with optional redundant starters)	8, 1110, AGM
Battery voltage (DC)	12
Air Requirements	60 Hz
Radiator-cooled cooling air, m³/min. (scfm)‡	1980 (69923)
Cooling air required for generator set when equipped with city water cooling or remote radiator, based on 14°C (25°F)	
rise, m³/min. (scfm) ‡	1076 (37993)
Combustion air, m³/min. (cfm) Heat rejected to ambient air:	119 (4202)
Engine, kW (Btu/min.)	204 (11772)
Alternator, kW (Btu/min.)	93 (5325)

Alternator Spe	cifications	60 Hz
Туре		4-Pole, Rotating-Field
Exciter type		Brushless, Permanent-
		Magnet Pilot Exciter
Voltage regulate	or	Solid-State, Volts/Hz
Insulation:		NEMA MG1, UL 1446,
		Vacuum Pressure
		Impregnated (VPI)
Material		Class H, Synthetic,
-		Nonhygroscopic
Temperature ris		130°C, 150°C Standby
Bearing: quantit	y, type	1, Sealed
Coupling type	P	Flexible Disc
Amortisseur win	0	Full
	ng type (up to 600 V)	Random Wound
	ng type (above 600 V)	Form Wound
Rotor balancing		125%
0 0	on, no-load to full-load	±0.25%
Jnbalanced loa	d capability	100% of Rated Standby
		Current
Peak motor star	•	(35% dip for voltages below)
480 V	KH03850TO4D	5351
480 V	KH04590TO4D	6030
480 V	KH04920TO4D	6509
480 V	KH05740TO4D	6749
480 V	KH06810TO4D	8466
480 V KH06810TO4D		8466
4160 V	KH05641TO4D	NA
4160 V	KH06721TO4D	NA

Alternator Standard Features

- The pilot-excited, permanent magnet (PM) alternator provides superior short-circuit capability.
- · All models are brushless, rotating-field alternators.
- NEMA MG1, IEEE, and ANSI standards compliance for temperature rise and motor starting.
- Sustained short-circuit current of up to 300% of the rated current for up to 10 seconds.
- Sustained short-circuit current enabling downstream circuit breakers to trip without collapsing the alternator field.
- Self-ventilated and dripproof construction.
- Superior voltage waveform from two-thirds pitch windings and skewed stator.
- Brushless alternator with brushless pilot exciter for excellent load response.

NOTE: See TIB-102 Alternator Data Sheets for alternator application data and ratings, efficiency curves, voltage dip with motor starting curves, and short circuit decrement curves.

 \pm Air density = 1.20 kg/m³ (0.075 lbm/ft³)

Controllers



APM802 Controller

Provides advanced control, system monitoring, and system diagnostics for optimum performance and compatibility.

- 12-inch graphic display with touch screen and menu control provide easy local data access
- Measurements are selectable in metric or English units
- User language is selectable
- Two USB ports allow connection of a flash drive, mouse, or keypad
- Electrical data, mechanical data, and system settings can be saved to a flash drive
- Ethernet port allows connection to a PC type computer or Ethernet switch
- The controller supports Modbus® RTU and TCP protocols
- NFPA 110 Level 1 capability

Refer to G6-152 for additional controller features and accessories.

Modbus® is a registered trademark of Schneider Electric.



APM603 Controller

Provides advanced control, system monitoring, and system diagnostics for optimum performance and compatibility.

- 7-inch graphic display with touch screen and menu control provides easy local data access
- · Measurements are selectable in metric or English units
- Paralleling capability to control up to 8 generators on an isolated bus with first-on logic, synchronizer, kW and kVAR load sharing, and protective relays
 - Note: Parallel with other APM603 controllers only
- Generator management to turn paralleled generators off and on as required by load demand
- Load management to connect and disconnect loads as required
- Controller supports Modbus® RTU, Modbus® TCP, SNMP and BACnet®
- Integrated voltage regulator with ±0.25% regulation
- Built-in alternator thermal overload protection
- UL-listed overcurrent protective device
- NFPA 110 Level 1 capability

Refer to G6-162 for additional controller features and accessories.

BACnet® is a registered trademark of ASHRAE.

Codes and Standards

- Engine-generator set is designed and manufactured in facilities certified to ISO 9001.
- Generator set meets NEMA MG1, BS5000, ISO, DIN EN, and IEC standards, NFPA 110.
- Engine generator set is tested to ISO 8528-5 for transient response.
- The generator set and its components are prototype-tested, factory-built, and production-tested.

Third-Party Compliance

• Tier 2 EPA-Certified for Stationary Emergency Applications

Available Approvals and Listings

- ☐ California OSHPD Pre-Approval
- □ cULus (UL 2200 and CSA)
- ☐ IBC Seismic Certification
- □ Florida Dept. of Environmental Protection (FDEP) Compliance (fuel tanks only)

Warranty Information

- A standard three-year unlimited-hour limited warranty for standby applications in the U.S. And Canada. Five-year basic, five-year comprehensive, and ten-year extended limited warranties are also available.
- A standard two-year or 8700-hour limited warranty for prime power applications.

Available Warranties for Standby Applications

- □ 5-Year Basic Limited Warranty
- ☐ 5-Year Comprehensive Limited Warranty
- 10-Year Major Components Limited Warranty

Standard Features

- Closed Crankcase Ventilation (CCV) Filters
- Customer Connection
- Generator Heater (4160 Volt)
- Integral Vibration Isolation
- Local Emergency Stop Switch
- Oil Drain and Coolant Drain Extension
- · Operation and Installation Literature

Industrial Diesel Generator Set - KD150

Tier 2 EPA-Certified for Stationary Emergency Applications

Available Options

A	valiable Options			
	Circuit Breakers			Electrical System
0	Thermal Magnetic Trip Electronic Trip (LI) Electronic Trip with Short	Rating 80% 100% Operation Manual Electrically Operated (for paralleling)	0 0 0 0 0	Battery, AGM (kit with qty. 4) Battery, AGM (kit with qty. 8) Battery Charger Battery Heater; 80 W, 120 V, 1Ph Battery Rack and Cables Generator Heater (up to 600 Volt) Redundant Starters
_ 	Circuit Breaker Mounting Generator Mounted Remote Mounted Bus Bar (for remote mounted bre	akers)		Fuel System Flexible Fuel Lines Restriction Gauge (for fuel/water separator) Literature
<u> </u>	- (/	cuit Breakers		General Maintenance NFPA 110 Overhaul
_	Engine Type			Production
	KDxxxx Tier 2 EPA-Certified Eng KDxxxx-F Fuel Optimized Engine		_	Miscellaneous
	Approvals and Listings	starting (EDED) Compliance	0 0 0	Air Cleaner, Heavy Duty (loose) Air Cleaner Restriction Indicator Alternator Air Filter (will reduce generator set rating by 7%) Automatic Oil Replenishment System Engine Fluids (oil and coolant) Added Rated Power Factor Testing
_	(fuel tanks only)	otection (FBEF) compliance		Electrical Package (Requires Enclosure selection)
	Hurricane Rated Enclosure			Basic Electrical Package (select 1 Ph or 3 Ph)
	Open Unit		_ _ _	Wire Battery Charger (1 Ph) Wire Block Heater (select 1 Ph or 3 Ph) Wire Controller Heater (1 Ph) Wire Generator Heater (1 Ph)
	Exhaust Silencer, Critical (kits: Pr Exhaust Silencer, Hospital (kits: F Flexible Exhaust Connector, Stain	PA-361626 qty. 2)		Warranty (Standby Applications only) 5-Year Basic Limited Warranty 5-Year Comprehensive Limited Warranty
	Controller		_	10-Year Major Components Limited Warranty
	Input/Output, Digital Input/Output, Thermocouple (star Load Shed (APM802 only) Manual Key Switch Remote Emergency Stop Switch Lockable Emergency Stop Switch Remote Serial Annunciator Pane		0	Other

Cooling System


- ☐ Block Heater; 9000 W, 208 V, (Select 1 Ph or 3 Ph) #
- ☐ Block Heater; 9000 W, 240 V, (Select 1 Ph or 3 Ph) #
- ☐ Block Heater; 9000 W, 380 V, 3 Ph *
- Block Heater; 9000 W, 480 V, (Select 1 Ph or 3 Ph) #
 - * Required for ambient temperatures below 10°C (50°F). Block heater kit includes air intake manifold grid heater.
- □ Radiator Guard and Duct Flange

Dimensions and Weights

Overall Size, max., L x W x H, mm (in.):

5799 x 2152 x 2480 (228.3 x 84.7 x 97.6) 12896 (28443)

Weight, radiator model, max. wet, kg (lb.):



NOTE: This drawing is provided for reference only and should not be used for planning installation. Contact your local distributor for more detailed information.

Sound Enclosures and Subbase Fuel Tank

Sound Level 1 Enclosure Standard Features


- Lift base or tank-mounted, aluminum construction enclosure with internal-mounted, exhaust silencers.
- Every enclosure has a sloped roof to reduce the buildup of moisture and debris.
- Sound attenuated enclosure that offers noise reduction using acoustic insulation, acoustic-lined air inlets and an acousticlined air discharge.
- Fade-, scratch-, and corrosion-resistant Power Armor[™] automotive-grade textured finish.
- Acoustic insulation that meets UL 94 HF1 flammability classification.
- Enclosure has large access doors that are hinged and removable which allow for easy maintenance.
- · Lockable, flush-mounted door latches.
- · Air inlet louvers reduce rain and snow entry.
- High wind bracing, 241 kph (150 mph).

Sound Level 2 Enclosure Standard Features


- Includes all of the sound level 1 enclosure features with the addition of up to 51 mm (2 in.) acoustic insulation material, intake sound baffles, vertical air discharge, and secondary silencers.
- Louvered air inlet and vertical outlet hood with 90 degree angles to redirect air and reduce noise.

Subbase Fuel Tank Features


- The fuel tank has a black powder-coat finish texture.
- The above-ground rectangular secondary containment tank mounts directly to the generator set, below the generator set skid (subbase).
- Both the inner and outer tanks have UL-listed emergency relief vents.
- Flexible fuel lines are provided with subbase fuel tank selection.
- The containment tank's construction protects against fuel leaks or ruptures. The inner (primary) tank is sealed inside the outer (secondary) tank. The outer tank contains the fuel if the inner tank leaks or ruptures.
- The above ground secondary containment subbase fuel tank meets UL 142 requirements.
- Features include:
 - Additional fittings for optional accessories (gty. 3)
 - o Electrical stub-up area open to bottom
 - o Emergency inner and outer tank relief vents
 - o Fuel fill with lockable cap and 51 mm (2 in.) riser
 - Fuel leak detection switch
 - Fuel level mechanical gauge
 - o Fuel level sender
 - Normal vent
 - o Removable engine supply and return diptubes



Sound Level 1 Enclosure (Shown with available spill containment)



(Shown with available spill containment)



Subbase Fuel Tank (Top View)